


Stark Model AP-10 Purification System

- Flow rate – Compressors up to 5 CFM maximum
- Approximate volume of Processed Air – 10,000 cubic feet
- Traps – 1 each
- Purifier tower – 1 each 14" chamber (takes 10" cartridge)
- Cartridges – 65670 or 65240 (recommended)
- Configuration – Trap & One short purifier
- Wall mounted
- Internal plumbing included
- Connections - #4 JIC male or 1/4" FPT
- Dimensions – 28" x 6" x 20" High
- Weight – 60 pounds

Components

1. Trap
2. Relief valve
3. Trap drain valve
4. Check valve
5. Purifier chamber
6. Bleed valve
7. Pressure gauge
8. Back pressure valve



Recommended Cartridge change for 5 CFM compressor – every 10 hours
The amount of processed air for any purifier system always depends on the compressor condition and ambient air factors such as temperature and humidity.